

# Eaton XTCE032C10H

Catalog Number: XTCE032C10H

Eaton XT IEC contactor, 32A, 240 Vac, 50 Hz, 277V 60 Hz, 1NO, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	XTCE032C10H
<b>UPC</b>	<b>Product Length/Depth</b>
782116486144	3.425 in
<b>Product Height</b>	<b>Product Width</b>
3.898 in	1.85 in
<b>Product Weight</b>	<b>Warranty</b>
0.9 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	IEC 60947
CE Marked	CSA Certified
	EN 60947
	UL Listed

## Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

32A

### HP rating - max

3, 5, 5/ 10, 10, 20, 25 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

45 mm

### Terminals

Screw terminals

### Coil voltage

240-277 Vac, 50/60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

32 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_C 3D Model Xchange](#)

[XTCE\\_C 2D PDF](#)

[XTCE\\_C AutoCAD 2D Footprint](#)

[XTCE\\_C 2D Drawing Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE032C10H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)