

# Eaton XTCE065D00C

Catalog Number: XTCE065D00C

Eaton XT IEC contactor, 65A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 0NO-0NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	XTCE065D00C
<b>UPC</b>	<b>Product Length/Depth</b>
782116486601	2.244 in
<b>Product Height</b>	<b>Product Width</b>
5.945 in	4.567 in
<b>Product Weight</b>	<b>Warranty</b>
2.4 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Listed
CE Marked	CSA Certified
	IEC 60947
	EN 60947

## Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

65A

### HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

412-480 Vac, 50/60 Hz

### Coil voltage

415-480 Vac, 50/60 Hz

### Contact configuration

0 NO, 0 NC

### Continuous ampere rating

65 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_D 2D PDF](#)

[XTCE\\_D 3D Inventor](#)

[XTCE\\_D 2D Drawing Xchange](#)

[XTCE\\_D 3D Model Xchange](#)

[XTCE\\_D AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE065D00C](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCE065D00C

Catalog Number: XTCE065D00C

Eaton XT IEC contactor, 65A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 0NO-0NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

## General specifications



### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE065D00C

### UPC

782116486601

### Product Length/Depth

2.244 in

### Product Height

5.945 in

### Product Width

4.567 in

### Product Weight

2.4 lb

### Warranty

1 year

### Compliances

RoHS Compliant

CE Marked

### Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

65A

### HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

412-480 Vac, 50/60 Hz

### Coil voltage

415-480 Vac, 50/60 Hz

### Contact configuration

0 NO, 0 NC

### Continuous ampere rating

65 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

Eaton's Volume 5—Motor Control and Protection

### Drawings

XTCE\_D 2D PDF

XTCE\_D 3D Inventor

XTCE\_D 2D Drawing Xchange

XTCE\_D 3D Model Xchange

XTCE\_D AutoCAD 2D Footprint

### Specifications and datasheets

Eaton Specification Sheet - XTCE065D00C

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)