

# Eaton XTCE080FS1A

Catalog Number: XTCE080FS1A

Eaton XT IEC contactor, 80 A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15, 15/25, 30, 60, 75 hp(1/3PH@115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

## General specifications



### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE080FS1A

### UPC

786685365138

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

## defaultTaxonomyAttributeLabel

### Amperage Rating

80A

### HP rating - max

7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

90 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

80 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

Eaton's Volume 5—Motor Control and Protection

### Drawings

XTCE\_F 3D Inventor

XTCE\_F AutoCAD 2D Footprint

XTCE\_F 2D PDF

XTCE\_F 3D Model Xchange

XTCE\_F 2D Drawing Xchange

### Specifications and datasheets

Eaton Specification Sheet - XTCE080FS1A



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton XTCE080FS1A

Catalog Number: XTCE080FS1A

Eaton XT IEC contactor, 80 A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15, 15/25, 30, 60, 75 hp(1/3PH@115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

## General specifications



### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE080FS1A

### UPC

786685365138

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

## defaultTaxonomyAttributeLabel

### Amperage Rating

80A

### HP rating - max

7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH  
@115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

90 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

80 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

Eaton's Volume 5—Motor Control and Protection

### Drawings

XTCE\_F 3D Inventor

XTCE\_F AutoCAD 2D Footprint

XTCE\_F 2D PDF

XTCE\_F 3D Model Xchange

XTCE\_F 2D Drawing Xchange

### Specifications and datasheets

Eaton Specification Sheet - XTCE080FS1A



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)