

Specifications



Photo is representative



Eaton XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE095FS1A
UPC	786685365145
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	1 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed CSA Certified EN 60947 IEC 60947



Powering Business Worldwide

Product specifications

AMPERAGE RATING	95A
HP RATING - MAX	40, 50, 100, 125 hp (3PH @200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	90 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	95 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCE095FS1A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE095FS1A
UPC	786685365145
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	1 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed CSA Certified EN 60947 IEC 60947



Powering Business Worldwide

Product specifications

AMPERAGE RATING	95A
HP RATING - MAX	40, 50, 100, 125 hp (3PH @200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	90 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	95 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCE095FS1A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

