

# Specifications



Photo is representative

## Eaton XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE115GS1A
<b>UPC</b>	786685365152
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed EN 60947 IEC 60947



Powering Business Worldwide

### Product specifications

**AMPERAGE RATING** 115A

### Resources

<b>HP RATING - MAX</b>	10, 25, 25/ 40, 50, 100, 100 hp (1/3PH @ 115,200,230/200,230,460,575 V)
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Full voltage non-reversing contactor
<b>FREQUENCY RATING</b>	50-60 Hz
<b>FRAME SIZE</b>	90 mm
<b>TERMINALS</b>	Screw terminals
<b>COIL</b>	110-120 Vac, 50/60 Hz
<b>COIL VOLTAGE</b>	110-120 Vac, 50/60 Hz
<b>CONTACT CONFIGURATION</b>	1 NO, 1 NC
<b>CONTINUOUS AMPERE RATING</b>	115 A
<b>SERIES</b>	XT IEC
<b>OPERATION</b>	Non-reversing

---

**SPECIFICATIONS AND  
DATASHEETS**

---

[Eaton Specification Sheet -  
XTCE115GS1A](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.



# Specifications



Photo is representative

## Eaton XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE115GS1A
<b>UPC</b>	786685365152
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed EN 60947 IEC 60947



Powering Business Worldwide

### Product specifications

**AMPERAGE RATING** 115A

### Resources

<b>HP RATING - MAX</b>	10, 25, 25/ 40, 50, 100, 100 hp (1/3PH @ 115,200,230/200,230,460,575 V)
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Full voltage non-reversing contactor
<b>FREQUENCY RATING</b>	50-60 Hz
<b>FRAME SIZE</b>	90 mm
<b>TERMINALS</b>	Screw terminals
<b>COIL</b>	110-120 Vac, 50/60 Hz
<b>COIL VOLTAGE</b>	110-120 Vac, 50/60 Hz
<b>CONTACT CONFIGURATION</b>	1 NO, 1 NC
<b>CONTINUOUS AMPERE RATING</b>	115 A
<b>SERIES</b>	XT IEC
<b>OPERATION</b>	Non-reversing

---

**SPECIFICATIONS AND  
DATASHEETS**

---

[Eaton Specification Sheet -  
XTCE115GS1A](#)

---



---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest  
product and support information.

All other trademarks are property of  
their respective owners.

