

# Eaton XTCR080F11A

Catalog Number: XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR



## General specifications

### Product Name

Eaton XT IEC contactor

### UPC

782116356126

### Product Height

6 in

### Product Weight

4.7 lb

### Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

### Catalog Number

XTCR080F11A

### Product Length/Depth

9.5 in

### Product Width

6.5 in

### Compliances

CE Marked

RoHS Compliant

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

80A

### HP rating - max

7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

80 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCR080F11A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCR080F11A

Catalog Number: XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR



## General specifications

### Product Name

Eaton XT IEC contactor

### UPC

782116356126

### Product Height

6 in

### Product Weight

4.7 lb

### Certifications

UL Listed  
CSA Certified  
IEC 60947  
EN 60947

### Catalog Number

XTCR080F11A

### Product Length/Depth

9.5 in

### Product Width

6.5 in

### Compliances

CE Marked  
RoHS Compliant

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

80A

### HP rating - max

7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

80 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCR080F11A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)