



# YA25L4BOX, 1/0 AWG, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window

By Burndy  
Catalog # [YA25L4BOX](#)



Copper Compression lug, 1 Hole w/ Inspection Window, 1/0 AWG, 3/8" Stud, Short Barrel, Tin Plated.

## Application

Wire Termination

## General

Color Code	Pink
Connector Type	STANDARD BARREL
Die Index	12
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"><li>Chamfered</li><li>Skived</li></ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810553503
UPC 12 Digit	7818105535033

## Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.74 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.09 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1

## Product Assets

- [3D Models - YA25L4BOX\\_MODEL-PDF](#)
- [3D Models - YA25L4BOX\\_MODEL-IGES](#)
- [3D Models - YA25L4BOX\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD079848](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size fraction 3/8  
Dimension - Stud Size inch 3/8  
Dimension - Z inch 0.33 in  
Physical Attribute - Tongue Straight  
Angle

---



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA25L4BOX-SPEC-EN | REV 6/2023