



YA262N, 2/0 AWG, CU, 2-hole, 1/2" studs, 1-3/4" spacing, Long Barrel

By Burndy
Catalog # [YA262N](#)

2/0 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.



General

EU RoHS Indicator	Yes
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated

Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper Str Size Range	2/0 AWG
-----------------------------------	---------

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - YA262N_MODEL-PDF](#)
- [3D Models - YA262N_MODEL-STEP](#)
- [3D Models - YA262N_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD..031189-02](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA262N-SPEC-EN | REV 6/2023