

YA28LBOX

by Burndy
Catalog ID: YA28LBOX

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 4/0 AWG, 1/2" Stud, Short Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 1-1/8 IN, Finish: Electro-Tin Plated, Package: Box, Temperature Rating: 90 DEG C, Die Index: 15, Tongue Angle: Straight, Color Code: Purple, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W28VT, W28RT, X28RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W28VT, W28RT Die, (2), X28RT Die, (3), Y35, Y39, Y750, PAT750 Tool, U28RT Die, (1), Y46 Tool, U28RT Die With PUADP-1 Adapter, (1), Dieless Tools (number Of Crimps): Y644HS, MY29-3, MY29-11 Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V, MRC840 Tool, (2), Conductor Type: Commercial Stranded Copper



Product Details

General

Application	For Code Conductor
Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810554104
UPC 12 Digit	7818105541044

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm

Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.46 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)