

YA2CL2BOX

by Burndy
Catalog ID: YA2CL2BOX

Prop 65 Notice

Copper Compression lug, 1 Hole w/ Inspection Window, 2 AWG, 1/4" Stud, Short Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 15/16 IN, Package: Box, Tongue Angle: Straight, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Die Index: 10, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (1), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (1), Color Code: Brown, Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11, MRC840 Tool, (1), YIMRTC Tool, (2), Conductor Type: Commercial Stranded Copper



Product Details

General

Application	For Code Conductor
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810551752
UPC 12 Digit	7818105517522

Dimensions

Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.64 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm

Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.61 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)