

# Compression Terminal

By Burndy  
Catalog # [YA6CLBOX](#)



6 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, BLUE Color Code, 7 or 374 Die Index.

## Application

Wire Termination

## General

Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810552759
UPC 12 Digit	7818105527599

## Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.54 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.45 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	9/16 in
Dimension - Stud Size fraction	1/4

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
Minimum Pack Quantity	50

## Product Assets

- [3D Models - YA6CLBOX\\_MODEL-PDF](#)
- [3D Models - YA6CLBOX\\_MODEL-IGES](#)
- [3D Models - YA6CLBOX\\_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - sd079848-02](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 1/4 in  
Dimension - Z inch 0.33 in  
Physical Attribute - Tongue Straight  
Angle

---



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA6CLBOX-SPEC-EN | REV 6/2023