



**BURNDY Catalog Number**  
**UPC Number**

YAEV10T2  
7818100278200

**Description**

12-10 NYL. HVY DTY RING, 5/16  
IN Stud

**Status**

Active

**Web Use**

BURNDY Product Line

**Dimensional**

Length (in) 1.36  
Tongue Type Ring  
Stud Size (in) 5/16  
Pad Width (in) 0.53

**Electrical**

Max Voltage Rating 600

**General**

**Product Description**

Copper Lug, Ring Tongue, 1 Hole  
w/ Inspection Hole, AN 12-10,  
5/16" Stud, Insulated, Short  
Barrel, Tin Plated, 600 Volts Max.

**Conductor(s)**

Aircraft Cable Size (Range) AN 12-AN 10  
Copper Solid Size (Range) N/A  
Navy Cable Size (Range) N/A  
Copper Stranded (Range) 12-10

**Physical**

Type of Plating Tin  
Connector Type Terminal  
Color Code Yellow  
Insulation Type Nylon  
Plated (Yes or No) Y

**Approvals / Certifications**

Industry Standards Military Specified (Mil-  
Spec),UL486  
UL Listed Y  
CSA Certified N  
ROHS Compatible Compliant  
UL Recognized N  
CULUS N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175