



BURNDY Catalog Number
UPC Number

YAEV8CL
7818100277388
8 AWG NYL HVYDTY RING
10,1.397 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Length (in) 1.40
Tongue Type Ring
Stud Size (in) #10
Pad Width (in) 0.41

Electrical

Max Voltage Rating 600

General

Product Description
Copper Lug, Ring Tongue, 1 Hole w/ Inspection Hole, 8 AWG, #8-#10 Stud, Insulated, Short Barrel, Tin Plated, 600 Volts Max.

Conductor(s)

Aircraft Cable Size (Range) AN 8
Copper Solid Size (Range) N/A
Navy Cable Size (Range) N/A
Copper Stranded (Range) 8

Physical

Type of Plating Tin
Connector Type Terminal
Color Code Red
Insulation Type Nylon
Plated (Yes or No) Y

Approvals / Certifications

Industry Standards Military Specified (Mil-Spec),UL486
UL Listed Y
CSA Certified N
ROHS Compatible Compliant
UL Recognized N
Mil-Spec Class Code Class 1
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175