



BURNDY Catalog Number
UPC Number

YAV2CL2BOX
7818105396511
2AWG HVYDTY RING 5/16
ST,1.722 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.72
Tongue Type	Ring
Stud Size (in)	5/16
Pad Width (in)	0.69
Strip Length	5/8"

General

Product Description	Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-2 Flex, 5/16" Stud, Short Barrel, Tin Plated
---------------------	---

Other

Installation Tooling	Non-Ratchet:MY28,MY29-11
Bulk Package	YAV2CL2

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
Mil-Spec Class Code	Class 1
CULUS	N
Industry Standards	UL467, Military Specified (Mil-Spec)

Conductor(s)

Aircraft Cable Size (Range)	AN 2
Copper Solid Size (Range)	2
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	2

Physical

Type of Plating	Tin
Connector Type	Terminal
Plated (Yes or No)	Y

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175