



**BURNDY Catalog Number** YGHA312N  
**UPC Number** 7818101259600  
**Description** CU 350, HVY DUTY TERM  
**Status** Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Thickness	0.43
B Length (in)	1.18
D - in	3.00
Pad Width (in)	1.62
Stud Size (Fraction)	1/2
E - in	1.75
General	
Product Description	Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe Hole, 350 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	350 kcmil
Physical	
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Index Number	20
Approvals / Certifications	
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B,UL467,IEEE 837
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175