



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YS28LBOX 4/0AWG Butt Splice

Burndy LLC

Catalog Number	YS28LBOX
Manufacturer	Burndy LLC
Description	4/0 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Purple Color Code, 15 Die Index.
Weight per unit	0.1000 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	15
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	PURPLE
Finish	Tin-Plated

### Descriptions

Description	4/0AWG BUTT SPLICE
extra long description	BUR YS28LBOX 4/0 STR. HYLINK-SPLICE
Long Description	4/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, PURPLE Color Code, 15 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length: Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, Oil Stop: No, Color Code: Purple, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Tapered End: No, Die Index: 15 Element A, Wire Strip Length: 1-1/16 IN, Conductor Type: Commercial Stranded Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical:

### Manufacturer Information

Brand	BURNDY
GTIN	00781810556757
Manufacturers Part Number	YS28LBOX
UPC	781810556757

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B