



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS39 750 Comp Cu Butt Splice

Burndy LLC

Catalog Number	YS39
Manufacturer	Burndy LLC
Description	750 Kcmil Cu, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Black Color Code, 24 Die Index.
Weight per unit	0.9400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	24
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BLACK
Finish	Tin-Plated

Descriptions

Description	750 COMP CU BUTT SPLICE
extra long description	BUR YS39 BUTT SPLICE LONG 750
Long Description	750 kcmil CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, BLACK Color Code, 24 Die Index.
Product Type	Splice
Special Features	Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Color Code: Black, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4), Oil Stop: No, Tapered End: No, Die Index: 24 Element A, Cond

Manufacturer Information

Brand	BURNDY
GTIN	00781810526859
Manufacturers Part Number	YS39
UPC	781810526859

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS, Long Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.94

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B