



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YSHG4429  
 7818101286577  
 9 REBAR-250/2 DBL H-TAP  
 Active

**Web Use**  
 BURNDY Product Line

Product Description

**General**

Copper Compression Double H-Tap Connector, 2 AWG - 250 kcmil (Tap), #8 & #9 Rebar/ 1" Ground Rod

**Conductor(s)**

Rebar Size Tap (Range) N/A  
 Rod Size Tap (Range) N/A  
 Copper Tap Range 2 AWG-250 kcmil  
 Copper Stranded Run (Range) N/A  
 Rod Size Run (Range) 1 in  
 Rebar Run Size (Range) 8 -9

**Approvals / Certifications**

Rated for Direct Burial Y  
 UL Listed Y  
 CSA Certified N  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N  
 Industry Standards UL467

**Physical**

Type of Plating Unplated  
 Plated (Yes or No) N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175