

# KT-EMRG-LED-12-1200-K1 constant wattage led emergency back-up







### **DESCRIPTION**

LED Emergency Back-Up Driver Kit | 12W Output | 120-277V Input

**DRIVER TYPE:** Constant Wattage LED Emergency

MAX. OUTPUT POWER: 12W

INPUT VOLTAGE: 120-277Vac ±10%

**OUTPUT VOLTAGE:** 12~41Vdc

**OUTPUT CURRENT:** 1000-200mA

**WARRANTY:** 5 Years



#### PRODUCT FEATURES

- Drives dedicated LED load (included) at 12W for a minimum of 90 minutes
- Meets FCC Part 15 (Class B) consumer limits
- Short circuit overload and open load protection
- Suitable for dry and damp locations
- Evaluated to UL 924 standards

• Operating temperature: 0°C/32°F to 50°C/122°F

• Input frequency: 50/60 Hz

• Test switch/Charging indicator light

• Battery pack with quick connect: NiCd

• Battery capacity: 3000mAh


Emergency Pack does not meet CEC T20 requirements. Not to be sold or offered for sale in California, except when sold wholesale in California for final retail sale outside the state.

### **ELECTRICAL SPECIFICATIONS**

	INPUT CHARACTERISTICS			OUTPUT CHARACTERISTICS		
Family	Input Voltage	Power Factor	Max. Current	Max. Output Power	Rated Output Current	Output Voltage
12W	120-277Vac	≥0.5	0.07A @ 120V	12W	1000mA-200mA	12~41Vdc

Emergency pack designed to deliver 12W to a constant current LED load. Approximate output is 1200 lumens, assuming a nominal minimum efficacy of 100 lm/W.


### MECHANICAL SPECIFICATIONS



### CASE DIMENSIONS

L (Length)	6.46"		
W (Width)	1.37"		
H (Height)	1.00"		
M (Mounting)	6.00"		

Case Style: L7 Case Material: Metal



### BATTERY DIMENSIONS

L (Length)	9.45"	
W (Width)	2.23"	
H (Height)	1.02"	
M (Mounting)	8.91"	

### **MODULE SPECIFICATIONS**

Catalog Number: KTLM-240-L8-850-24A

Length	8.00"	
Width	0.70"	
Number of LEDs	24	
Color Temperature	5000K	




# KT-EMRG-LED-12-1200-K1 CONSTANT WATTAGE LED EMERGENCY BACK-UP

### KIT WIRING SPECIFICATIONS

### STANDARD LEAD LENGTHS\*

Input	Black, White, White/Black: 12" #18AWG		
Outmut	Red, Blue: 24" #18AWG		
Output	Brown: 24" #20AWG		
Test Button	Red, Blue: 24" #22AWG		

<sup>\*</sup> Consult Keystone for special lead length requirements.





### KT-EMRG-LED-12-1200-K1 CONSTANT WATTAGE LED EMERGENCY BACK-UP

### **ORDERING INFORMATION**

ORDER CODE	DESCRIPTION	PACKAGING STYLE	PACK QUANTITY	ITEM STATUS
KT-EMRG-LED-12-1200-K1-IP	LED Emergency Driver with Battery and 0.7" $\times$ 8" 1200 lumen LED Module	Individually Packaged	1	Active

### **CATALOG NUMBER BREAKDOWN**

### KT-EMRG-LED-12-1200-K1-IP

1 2 3 4 5 6 7

- 1 Keystone Technologies
- 2 Emergency Back-up Driver
- 3 LED Driver
- 4 Wattage Family
- 5 Nominal Lumen Output
- 6 Kit
- 7 Packaging Style