



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LC4521LA 120V Photo Control

Intermatic Inc.

Catalog Number	LC4521LA
Manufacturer	Intermatic Inc.
Description	Locking Type Thermal Photocontrol, 120 V, Spark Arrestor
Weight per unit	0.2580 (lbs/each)
Product Category	Lighting Photocells

Features

connection	Lock Type
Connection Type	3-Prong Plug
supply voltage	120

Material, Color, and Finish

Color	Translucent
-------	-------------

Dimensions and Weight

Size	3 DIAMETER X 2-3/4 HEIGHT IN, 7.6 DIAMETER X 7 HEIGHT CM
------	--

Descriptions

Description	120V PHOTO CONTROL
extra long description	INT-MAT LC4521LA Locking Type Therm
Features	These photocontrols install on light fixtures with ANSI C136.10 NEMA receptacles commonly found on street light fixtures. Locking type design facilitates fast installation and replacement of photocontrol.
Long Description	Locking Type Thermal Photocontrol, 120 V, Spark Arrestor
Product Type	Locking Type Thermal Photocontrol, 120 V, Spark Arrestor
Special Features	Features: Cadmium Sulfide Photocell, Polypropylene Housing with UV Protection, 2400 Volt Open Type Spark Gap Arrestor

Manufacturer Information

Brand	Intermatic Inc.
GTIN	00078275002661
Manufacturers Part Number	LC4521LA
UPC	078275002661

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	TwistLock Photocell

Packaging

Carton	1
Package	12
Weight Per each	0.258



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Dusk to Dawn Lighting Control
Frequency Rating	50/60
Mounting	Twistlock Mount
Operating Temperature standard	-20 to +104 DEG F, -29 to +40 DEG C UL Recognized, CSA, Title CA 20 Listed, California Title 24 Compliant