



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WT41 Wiretwist Wire Connector, WT4 Yellow, 100/Box *Ideal*

Catalog Number	WT41
Manufacturer	Ideal
Description	Wire Twist Connector, (2) #18 Awg Conductor Size, (2) #12 Awg Conductor Size, Yellow Insulation Color, +221 °F Operating Temperature, 2 to 5 Conductors, 600 V Ac, 0.41 LB
Weight per unit	0.4100 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Number of Conductors	2 to 5
Voltage Rating	600

### Material, Color, and Finish

Color	Yellow
-------	--------

### Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT4 YELLOW, 100/BOX
extra long description	IDEAL WT4-1 WIRE-TWIST CONN.,YELLOW
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing

### Manufacturer Information

Brand	Buchanan
GTIN	00781789610061
UPC	781789610061

### Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	----------------------------------------

### Availability

minimum qty	100
-------------	-----

### Packaging

Carton	100
Package	1000
Weight Per each	0.41



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS