

Item Number 0152511**Saf-T-Bar®**

For New Construction Applications


Attic Access Required

Specifications

- Can be used with engineered truss
- Fits all ceiling fans
- Fits 16" to 24" ceiling joists
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 90 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less
- Position box anywhere along the brace
- Heavy duty, all metal, dual mount* electrical box
- 1-1/2" box depth, 15.5 cubic inch wiring capacity
- Six 1/2" Romex® or conduit knockouts; 1 Romex® connector
- Includes Saf-T-Cap® to protect inner workings during drywall installation or painting
- Includes mounting hardware and instructions

**Pack Information**

- Bulk Packed
- 12 Per Cut Case



Includes Mounting Hardware



Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC® Safety Codes.

* Dual Mount = Box is threaded for #8-32 (ideal for box covers and lightweight fixtures) and #10-24 screws (ideal for heavier fixtures and ceiling fans).

Romex® is a registered trademark of Southwire Company.

*Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.***Call 1-800-999-2226 or visit www.westinghouselighting.com.**

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

Item Number 0152511

Saf-T-Bar®

For New Construction Applications

Attic Access Required


Specifications

- Can be used with engineered truss
- Fits all ceiling fans
- Fits 16" to 24" ceiling joists
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 90 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less
- Position box anywhere along the brace
- Heavy duty, all metal, dual mount* electrical box
- 1-1/2" box depth, 15.5 cubic inch wiring capacity
- Six 1/2" Romex® or conduit knockouts; 1 Romex® connector
- Includes Saf-T-Cap® to protect inner workings during drywall installation or painting
- Includes mounting hardware and instructions



Pack Information

- Bulk Packed
- 12 Per Cut Case



Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC® Safety Codes.

* Dual Mount = Box is threaded for #8-32 (ideal for box covers and lightweight fixtures) and #10-24 screws (ideal for heavier fixtures and ceiling fans).

Romex® is a registered trademark of Southwire Company.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

® WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.