ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

# LC4521LA 120V Photo Control

*Intermatic Inc.*

| | |
|---|---|
| Catalog Number | LC4521LA |
| Manufacturer | Intermatic Inc. |
| Description | Locking Type Thermal Photocontrol, 120 V, Spark Arrestor |
| Weight per unit | 0.2580 (lbs/each) |
| Product Category | Lighting Photocells |

## Features

| | |
|---|---|
| connection | Lock Type |
| Connection Type | 3-Prong Plug |
| supply voltage | 120 |

## Material, Color, and Finish

| | |
|---|---|
| Color | Translucent |

## Dimensions and Weight

| | |
|---|---|
| Size | 3 DIAMETER X 2-3/4 HEIGHT IN, 7.6 DIAMETER X 7 HEIGHT CM |

## Descriptions

| | |
|---|---|
| Description | 120V PHOTO CONTROL |
| extra long description | INT-MAT LC4521LA Locking Type Therm |
| Features | These photocontrols install on light fixtures with ANSI C136.10 NEMA receptacles commonly found on street light fixtures. Locking type design facilitates fast installation and replacement of photocontrol. |
| Long Description | Locking Type Thermal Photocontrol, 120 V, Spark Arrestor |
| Product Type | Locking Type Thermal Photocontrol, 120 V, Spark Arrestor |
| Special Features | Features: Cadmium Sulfide Photocell, Polypropylene Housing with UV Protection, 2400 Volt Open Type Spark Gap Arrester |

## Manufacturer Information

| | |
|---|---|
| Brand | Intermatic Inc. |
| GTIN | 00078275002661 |
| Manufacturers Part Number | LC4521LA |
| UPC | 078275002661 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type | TwistLock Photocell |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.258 |

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Dusk to Dawn Lighting Control |
| Frequency Rating | 50/60 |
| Mounting | Twistlock Mount |
| Operating Temperature | -20 to +104 DEG F, -29 to +40 DEG C |
| standard | UL Recognized, CSA, Title CA 20 Listed, California Title 24 Compliant |