



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 073031208 D/T Strain Relf, .43-.54", 1/2" Ins *Hubbell Wiring Devices*

Catalog Number	073031208
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Dusttight Grips, Strain Relief, .43-.54", 1/2", Insulated
Weight per unit	0.1920 (lbs/each)
Product Category	Cable & Cord Grips

### Features

Cable Size	.43"-.54" (1.09-1.37)
Material	Aluminum Fittings, Galvanized Steel Mesh
pallet quantity	6480

### Material, Color, and Finish

Color	Metallic
-------	----------

### Dimensions and Weight

Size	Standard Sized
------	----------------

### Descriptions

Construction	Woven
Description	D/T STRAIN RELF, .43-.54", 1/2" INS
extra long description	HWDK 073031208 D/T STRAIN RELF, .43
Features	The development of Kellems strain relief grips spearheaded the concept of wire management solutions in 1927 and is still the most frequently chosen brand for use in a wide range of industries. A deluxe cord grip is a type of strain relief grip. Deluxe cord grips provide additional arc of bend control—rest outside the enclosure to reduce tension on cables, joints and terminals, as well as eliminating damage due to flexing, bending, twisting or vibration. This juncture—often called the rigid fatigue point—is

Long Description	Kellems Wire Management, Dusttight Grips, Strain Relief, .43-.54", 1/2", Insulated
------------------	---

Product Type	D/T Strain Relf, .43-.54", 1/2" Ins
Special Features	Insulated

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585330082
Manufacturers Part Number	073031208
series	Dust-Tight
UPC	783585330082



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Insulated, Wide Range

## Trade Size

Trade Size	0.5
------------	-----

## Packaging

Carton	1
Package	20
Weight Per each	0.192

## Uses, Certifications, and Standards

Application	Light Duty
Mounting standard	Locknut or Tapped Hole UL Listed