



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



OTS40 600V 40A 5 1/2X1 1/16 K5 Fuse

Mersen Fuses

Catalog Number	OTS40
Manufacturer	Mersen Fuses
Description	Fuse Ots - Class K5 - Fast-Acting 600VAC 300VDC 40A Ferrule Amp-Trap®
Weight per unit	0.2300 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

AC Voltage Rating	600
amperage rating	40
class	Class K5
connection	Ferrule
DC Voltage Rating	300
interrupt rating	50
Voltage Rating	600

Material, Color, and Finish

Body Material	PolyTube
---------------	----------

Dimensions and Weight

Size	5.5 x 1.06
------	------------

Descriptions

Description	600V 40A 5 1/2X1 1/16 K5 FUSE
extra long description	Mersen OTS40 Fuse OTS - Class K5 -
Features	One-Time OTS general purpose fuses provide low cost protection for feeder and branch-circuits serving lighting, heating, and other non-motor loads. OTS fuses will safely interrupt available short circuit currents up to 50,000 amperes in all ratings. OTS fuses are not rejection fuses and care should be taken to ensure that replacement fuses do not have lower interrupting ratings than original fuses.
Long Description	Fuse OTS - Class K5 - Fast-Acting 600VAC 300VDC 40A Ferrule Amp-Trap®
Product Type	Fuse Ots - Class K5 - Fast-Acting 600VAC 300VDC 40A Ferrule
Short Description	600V 40A 5 1/2x1 1/16 K5 FUSE
Special Features	Easy to read imprint label for quick recognition and replacement Low cost for high protection value



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Mersen
GTIN	00782001700768
Manufacturers Part Number	OTS40
UPC	782001700768

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	CLASS K5

Packaging

Carton	1
Package	10
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Feeders Branch circuits Resistive heating Residential and small commercial installations
Mounting standard	Clip UL Listed to Standard 248-9 File E2137 CSA Certified to Standard C22.2 No. 248.9 (The Canadian Electrical Code requires these fuses in ratings 15 through 60A to be of the low melting point design use OTN 15-60.) Self-certified for DC per UL248