



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10250T297LRP2A Pretest FV 120VAC Red Led - Plastic Lens

Eaton Corp

Catalog Number	10250T297LRP2A
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, Heavy-Duty Watertight and Oiltight Indicating Light, Pretest, Full Voltage Led, Nema 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V
Weight per unit	0.4000 (lbs/each)
Product Category	Pilot Light Complete Assemblie

### Features

actuator	PresTest
media	Yes

### Dimensions and Weight

Depth	2.6
Height	4.7
Size	30.5 MM
Width	2.2

### Descriptions

Description	PRESTEST FV 120VAC RED LED - PLASTIC LENS
extra long description	ETN 10250T297LRP2A PRESTEST FV 120V
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, PresTest, Full voltage LED, NEMA 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V
Product Type	Pretest FV 120VAC RD Led-Plastic Lens

### Manufacturer Information

Brand	Eaton
GTIN	00782114712573
Manufacturers Part Number	10250T297LRP2A
Model	Pushbutton
UPC	782114712573

### Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
----------------------	-------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Listed, CSA Certified, CE Marked