



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T397L III Pushbutton FV Order Led Separately

Eaton Corp

Catalog Number	10250T397L
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 30.5 MM, Heavy-Duty, 40 MM, Nema 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Led, Full Voltage (Without Lamp) Light Unit, Flush, Chrome Bezel, Bayonet Base
Weight per unit	0.2200 (lbs/each)
Product Category	Push Button Components

Features

dimensions	1.6300 IN X 1.5900 IN X 2.2500 IN
media	Yes

Dimensions and Weight

Height	2.25
Length	1.63
Size	40 mm
Width	1.59

Descriptions

Description	ILL PUSHBUTTON FV ORDER LED SEPARATELY
extra long description	ETN 10250T397L ILL PUSHBUTTON FV (O
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, LED, full voltage (without lamp) light unit, Flush, Chrome bezel, Bayonet base
Product Type	III Pushbutton FV (Order Led Separately)
Special Features	10250T series

Manufacturer Information

Brand	Eaton
GTIN	00782114753651
Manufacturers Part Number	10250T397L
UPC	782114753651

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.22

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	FLUSH
standard	CSA Certified,UL Listed,CE Marked