



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T51 30MM Cont BLK 1NC Amber *Eaton Corp*

Catalog Number	10250T51
Manufacturer	Eaton Corp
Description	Eaton 30.5 MM Heavy-Duty Watertight/Oiltight Push-Pull Unit, Class I Division 2, Standard Actuator, Plastic Bus, 1NO-1NC, Non-Illuminated, 2-Position, Maintained Push and Pull, 10250T Series
Weight per unit	0.0200 (lbs/each)
Product Category	Contact Blocks

Features

Contact Configuration	1 NO-1 NC
dimensions	2.0000 IN X 2.0000 IN X 2.0000 IN
media	Yes

Dimensions and Weight

Size	40 mm
------	-------

Descriptions

Description	30MM CONT BLK 1NC AMBER
extra long description	ETN 10250T5-1 OILTIGHT PUSH-PULL OP
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 30.5 mm Heavy-Duty Watertight/Oiltight Push-Pull Unit,Class I Division 2,Standard Actuator,Plastic Bus,1NO-1NC,Non-illuminated,2-position,Maintained push and pull,10250T Series
Product Type	Oiltight Push-Pull Operator

Manufacturer Information

Brand	Eaton
GTIN	00782113324449
Manufacturers Part Number	10250T5-1
UPC	782113324449

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 0.02

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
..... Stationary Machinery and Equipment Outside Factory - Other

standard CSA Certified,UL Listed,CE Marked