



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



121054CHC Encl 12X10X5 N4 Encl *Cooper B-Line/Cable Tray*

Catalog Number	121054CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 12" Height, 5" Length, 10" Width, Nema 4, Hinged Cover, 4CHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	9.6 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

dimensions	5.0000 IN X 10.0000 IN X 12.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	10.00 In Width X 5.00 In Depth X 12.00 In Height
------	--

Descriptions

Description	ENCL 12X10X5 N4 ENCL
extra long description	B-LINE 12105-4CHC TYPE 4 JIC CONTIN
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 12" height, 5" length, 10" width, NEMA 4, Hinged cover, 4CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 4 Jic Continuous Hinge CVR Enc, 12X10X5
Special Features	Cont. piano hinge with s.s. door clamp,panel mount

Manufacturer Information

Brand	Eaton
GTIN	00782051740509
Manufacturers Part Number	12105-4CHC
UPC	782051740509

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	9.597

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control Ind Facilities & Factories - Facility: Automation and Monitoring Ind Facilities & Factories - Industrial Facilities/Factories - Other Commercial / Institutional Buildings / Structures - Critical Power Commercial / Institutional Buildings / Structures - Power Distribution and Controls Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Lighting and Lighting Controls Commercial / Institutional
Mounting	EXTERNAL FEET, WALL
nema rating	4
standard	NEMA,UL 50,CSA C22.2.