



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



123A 3/8-16 Small Body Beam Clamp

Topaz - Southwire LLC

Catalog Number	123A
Manufacturer	Topaz - Southwire LLC
Description	Beam Clamp, Single U Type; Malleable Iron Material; 3/4 Inch Max. Jaw Capacity; 300 LB Load Capacity; 3/8 Inch-16 Tpi Screw Size; Square Head Screw Type; Yes Supplied With Screw; Size 1.13 Inch W X 1.39 Inch D X 1.4 Inch H
Weight per unit	N/A
Product Category	Anchors & Fasteners

Features

Load Capacity	300 Lb
Material	Malleable Iron
Maximum Jaw Capacity	3/4 INCH
Screw Size	3/8 INCH-16 TPI
Screw Type	Square Head
Supplied with Screw	YES

Descriptions

Additional Information	Size 1.13 Inch W x 1.39 Inch D x 1.4 Inch H
Commodity Description	ANCHORS & FASTENERS
Description	3/8-16 SMALL BODY BEAM CLAMP
extra long description	SINGLE U TYPE; MALLEABLE IRON MATERIAL; 3/4 INCH MAX. JAW CAPACITY; 300 LB LOAD CAPACITY; 3/8 INCH-16 TPI SCREW SIZE; SQUARE HEAD SCREW TYPE; YES SUPPLIED WITH SCREW; SIZE 1.13 INCH W X 1.39 INCH D X 1.4 INCH H
Long Description	BEAM CLAMP, SINGLE U TYPE; MALLEABLE IRON MATERIAL; 3/4 INCH MAX. JAW CAPACITY; 300 LB LOAD CAPACITY; 3/8 INCH-16 TPI SCREW SIZE; SQUARE HEAD SCREW TYPE; YES SUPPLIED WITH SCREW; SIZE 1.13 INCH W X 1.39 INCH D X 1.4 INCH H
Product Type	Beam Clamp

Manufacturer Information

Brand	TOPAZ ELECTRIC CORP
GTIN	00751338107212
Manufacturers Part Number	123A
UPC	751338107212

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	SINGLE U



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 50

Weight Per each 0