



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **1224BK Switch, Hubpro, 4-Way, 20A 120/277V, BK** *Hubbell Wiring Devices*

Catalog Number	1224BK
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Hubbell- Pro Series, Toggle Switches, General Purpose Ac, Four Way, 20A 120/277V Ac, Back and Side Wired, Black
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

### **Features**

action	DPDT
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
operating cycles	50,000
pallet quantity	4050
Poles	Double Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540

### **Dimensions and Weight**

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

### **Descriptions**

Description	SWITCH, HUBPRO, 4-WAY, 20A 120/277V, BK
extra long description	HWDK 1224BK SWITCH, HUBPRO, 4-WAY,
Long Description	Switches and Lighting Controls, Hubbell- PRO Series, Toggle Switches, General Purpose AC, Four Way, 20A 120/277V AC, Back and Side Wired, Black
Product Type	Switch, Hubpro, 4-Way, 20A 120/277V, BK
Special Features	Standard Product



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585181493
Manufacturers Part Number	1224BK
series	Heavy Duty
UPC	783585181493

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed