



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353



1251LA SP Double-Throw Man. Switch, 20A, 120/277V, La *Pass & Seymour/Legrand*

Catalog Number	1251LA
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

amperage rating	20
connection	Side wire
Contact Configuration	NO
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Universal, LED, Halogen, Xenon, Fluorescent, CFL, Incandescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	1
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Light Almond
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353

Descriptions

Description	SP DOUBLE-THROW MAN. SWITCHTCH, 20A, 120/277V, LA
extra long description	P&S 1251LA MOM. CNT MAN CL 20A 120/
Features	Durable
Long Description	Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V.
Product Type	Mom. CNT Man CL 20A 120/277V (SPDT)
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007125153
Manufacturers Part Number	1251-LA
UPC	785007125153

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Manual Controller

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Industrial
Enclosure	Box or NEMA 1 sheet steel
Mounting standard	WALL CSA, UL, CULUS, UL listed