

Conduit Bodies

Threaded and Set Screw Bodies and Kits



| Hub Size | Unassembled (body only) Catalog No. | | | Assembled (with cover and gasket) Catalog No. | | | Box Quantity | Carton Quantity |
|-----------|--|-----------|-------------|--|-----------|-------------|--------------|-----------------|
| | Threaded | Set Screw | Combination | Threaded | Set Screw | Combination | | |
| LR | | | | | | | | |
| ½" | 11821 | 1871 | 13821 | 12821 | 12871 | 14821 | 10 | 50 |
| ¾" | 11822 | 11872 | 13822 | 12822 | 12872 | 14822 | 10 | 50 |
| 1" | 11823 | 11873 | 13823 | 12823 | 12873 | 14823 | 5 | 25 |
| 1¼" | 11824 | 11874 | 13824 | 12824 | 12874 | 14824 | — | 2 |
| 1½" | 11825 | 11875 | 13825 | 12825 | 12875 | 14825 | — | 2 |
| 2" | 11826 | 11876 | 13826 | 12826 | 12876 | 14826 | — | 1 |
| 2½" | | | | 12827 | | | — | 1 |
| 3" | | | | 12828 | | | — | 1 |
| 3½" | | | | 12829 | | | — | 1 |
| 4" | | | | 12830 | | | — | 1 |
| C | | | | | | | | |
| ½" | 11831 | 11881 | 13831 | 12831 | 12881 | 14831 | 10 | 50 |
| ¾" | 11832 | 11882 | 13832 | 12832 | 12882 | 14832 | 10 | 50 |
| 1" | 11833 | 11883 | 13833 | 12833 | 12883 | 14833 | 5 | 25 |
| 1¼" | 11834 | 11884 | 13834 | 12834 | 12884 | 14834 | — | 2 |
| 1½" | 11835 | 11885 | 13835 | 12835 | 12885 | 14835 | — | 2 |
| 2" | 11836 | 11886 | 13836 | 12836 | 12886 | 14836 | — | 1 |
| 2½" | | | | 12837 | | | — | 1 |
| 3" | | | | 12838 | | | — | 1 |
| T | | | | | | | | |
| ½" | 11841 | 11891 | 13841 | 12841 | 12891 | 14841 | 10 | 50 |
| ¾" | 11842 | 11892 | 13842 | 12842 | 12892 | 14842 | 10 | 50 |
| 1" | 11843 | 11893 | 13843 | 12843 | 12893 | 14843 | 5 | 25 |
| 1¼" | 11844 | 11894 | 13844 | 12844 | 12894 | 14844 | — | 2 |
| 1½" | 11845 | 11895 | 13845 | 12845 | 12895 | 14845 | — | 2 |
| 2" | 11846 | 11896 | 13846 | 12846 | 12896 | 14846 | — | 1 |
| 2½" | | | | 12847 | | | — | 1 |
| 3" | | | | 12848 | | | — | 1 |

CONDUIT BODIES AND COVERS

Conduit Bodies

Threaded and Set Screw Bodies and Kits



| Hub Size | Unassembled (body only) | | | Assembled (with cover and gasket) | | | Box Quantity | Carton Quantity |
|-----------|-------------------------|-----------|-------------|-----------------------------------|-----------|-------------|--------------|-----------------|
| | Catalog No. | | | Catalog No. | | | | |
| | Threaded | Set Screw | Combination | Threaded | Set Screw | Combination | | |
| LR | | | | | | | | |
| ½" | 11821 | 1871 | 13821 | 12821 | 12871 | 14821 | 10 | 50 |
| ¾" | 11822 | 11872 | 13822 | 12822 | 12872 | 14822 | 10 | 50 |
| 1" | 11823 | 11873 | 13823 | 12823 | 12873 | 14823 | 5 | 25 |
| 1¼" | 11824 | 11874 | 13824 | 12824 | 12874 | 14824 | — | 2 |
| 1½" | 11825 | 11875 | 13825 | 12825 | 12875 | 14825 | — | 2 |
| 2" | 11826 | 11876 | 13826 | 12826 | 12876 | 14826 | — | 1 |
| 2½" | | | | 12827 | | | — | 1 |
| 3" | | | | 12828 | | | — | 1 |
| 3½" | | | | 12829 | | | — | 1 |
| 4" | | | | 12830 | | | — | 1 |
| C | | | | | | | | |
| ½" | 11831 | 11881 | 13831 | 12831 | 12881 | 14831 | 10 | 50 |
| ¾" | 11832 | 11882 | 13832 | 12832 | 12882 | 14832 | 10 | 50 |
| 1" | 11833 | 11883 | 13833 | 12833 | 12883 | 14833 | 5 | 25 |
| 1¼" | 11834 | 11884 | 13834 | 12834 | 12884 | 14834 | — | 2 |
| 1½" | 11835 | 11885 | 13835 | 12835 | 12885 | 14835 | — | 2 |
| 2" | 11836 | 11886 | 13836 | 12836 | 12886 | 14836 | — | 1 |
| 2½" | | | | 12837 | | | — | 1 |
| 3" | | | | 12838 | | | — | 1 |
| T | | | | | | | | |
| ½" | 11841 | 11891 | 13841 | 12841 | 12891 | 14841 | 10 | 50 |
| ¾" | 11842 | 11892 | 13842 | 12842 | 12892 | 14842 | 10 | 50 |
| 1" | 11843 | 11893 | 13843 | 12843 | 12893 | 14843 | 5 | 25 |
| 1¼" | 11844 | 11894 | 13844 | 12844 | 12894 | 14844 | — | 2 |
| 1½" | 11845 | 11895 | 13845 | 12845 | 12895 | 14845 | — | 2 |
| 2" | 11846 | 11896 | 13846 | 12846 | 12896 | 14846 | — | 1 |
| 2½" | | | | 12847 | | | — | 1 |
| 3" | | | | 12848 | | | — | 1 |

CONDUIT BODIES AND COVERS