



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



14101RQD03 Vis Pol Reflex Comet With Quick Disconnect Connect Eaton Corp

Catalog Number	14101RQD03
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Polarized Retroreflective, Right Angle, Output On, Dual Key Micro, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, 4 Pin, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	1.0 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	Dual key micro
dimensions	3.0000 IN X 0.4700 IN X 0.7100 IN

Dimensions and Weight

Height	0.71
Length	3
Width	0.47

Descriptions

Description	VIS POL REFLEX COMET WITH QUICK DISCONNECT CONNECT
extra long description	ETN 14101RQD03 PHOTO SENSOR,POL RFL
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Polarized Retroreflective, Right Angle, Output ON, Dual key micro, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, 4 pin, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	Photo Sensor, Pol RFLX, Ra, Acdc, Conn

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113846675
Manufacturers Part Number	14101RQD03
UPC	782113846675

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature	-40° to 158°F (-40° to 70°C)
standard	UL Recognized,cUL Recognized