



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



1414N4PHSSG4 N4X J Box Hinge Cover W/PNL 8X6X4 304SS

Hammond MFG.

Catalog Number	1414N4PHSSG4
Manufacturer	Hammond MFG.
Description	N4X J Box, Hinge Cover W/Panel - 8 X 6 X 4 - 304 SS
Weight per unit	7.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

Material	Stainless Steel
----------	-----------------

Material, Color, and Finish

Color	Unpainted
-------	-----------

Dimensions and Weight

Size	8 in x 6 in x 4 in
------	--------------------

Descriptions

Description	N4X J BOX HINGE COVER W/PNL 8X6X4 304SS
extra long description	HMND 1414N4PHSSG4 1414N4PH STAINLES
Long Description	N4X J Box, Hinge Cover w/panel - 8 x 6 x 4 - 304 SS
Product Type	1414N4PH Stainless Steel
Special Features	Formed from 14 gauge 304 or 316 stainless steel. Smooth, continuously welded seams. Welded brackets provide for enclosure mounting. Continuous stainless steel hinged cover is secured with stainless steel clamps and screws. Seamless poured-in place gasket. All models include a removable 14 gauge inner panel. Tapped studs are provided for mounting inner panels. A bonding stud is provided on the door and a grounding stud is provided in the enclosure.

Manufacturer Information

Brand	Hammond MFG.
GTIN	00623980354408
Manufacturers Part Number	1414N4PHSSG4
UPC	623980354408

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	N4X J Box, Hinge Cover w/panel

Packaging

Carton	1
Weight Per each	7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Uses, Certifications, and Standards

Application

Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures. Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion may be a problem.

Mounting

WALL

nema rating

13;3R;4X

standard

CSA, UL, CE