

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301410038](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector, 2 Pole/3 Wire, NEMA 6-15, 250V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130141](#)  
 IP Rating      N/A  
 NEMA Configuration      NEMA 6-15  
 Overview      [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No      987650-8068  
 Product Name      Super-Safeway  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678870303  
 Woodhead      Yes

**Physical**

Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      No  
 Poles      2-pole/3-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      15.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      250V

**Material Info**

Engineering Number      1549



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130141 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301410038](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector, 2 Pole/3 Wire, NEMA 6-15, 250V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                                      LR6837  
 UL                                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                    [130141](#)  
 IP Rating                                N/A  
 NEMA Configuration                NEMA 6-15  
 Overview                               [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No        987650-8068  
 Product Name                         Super-Safeway  
 Receptacle Type                      Single  
 Specialty                                N/A  
 Type                                       Connector  
 UPC                                        78678870303  
 Woodhead                                Yes

**Physical**

Flange                                    No  
 Flip Lid                                  No  
 Gender                                  Female  
 Length                                  N/A  
 Locking Blade                         No  
 Poles                                      2-pole/3-wire

**Electrical**

Cord Type                                N/A  
 Current - Maximum per Contact    15.0A  
 GFCI                                      No  
 Lighted Connector                    No  
 Voltage - Maximum                    250V

**Material Info**

Engineering Number                    1549



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130141](#) Series