



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



155DC 1-1/2" Watertight Hub

Bridgeport Fittings

| | |
|------------------|--|
| Catalog Number | 155DC |
| Manufacturer | Bridgeport Fittings |
| Description | Threaded Hub, Zinc Die Cast, Size 1 1/2 Inch |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

Features

| | |
|-------------|--|
| Cable Entry | Through Rigid conduit into throat of fitting |
| Material | Zinc Die Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 1-1/2" WATERTIGHT HUB |
| extra long description | BPT 155-DC 1 1/2" THREADED HUB |
| Long Description | Threaded Hub, Zinc Die Cast, Size 1 1/2 Inch |
| Product Type | 1 1/2" Threaded Hub |
| Special Features | UL Type 4 Water Tight |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747091550 |
| Manufacturers Part Number | 155-DC |
| UPC | 781747091550 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type | Threaded Hubs |

Trade Size

| | |
|------------|-----|
| Trade Size | 1.5 |
|------------|-----|

Packaging

| | |
|-----------------|-----|
| Carton | 2 |
| Package | 20 |
| Weight Per each | 0.7 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

To secure threaded rigid service entrance conduit to box or enclosure. Insulated throat rated 105 degree c. UL listed Type 4 - Watertight. Suitable for Aluminum and Steel Rigid Conduit

standard

UL, CSA

Temperature Rating

105 C