



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1597TRWRGRY Radiant Self Test TR WR Gfci 15A 125V Gy

*Pass & Seymour/Legrand*

Catalog Number	1597TRWRGRY
Manufacturer	Pass & Seymour/Legrand
Description	Gfci Receptacles From The Radiant Registered Collection Self-Test Automatically Every Three Seconds to Ensure Reliable Protection From Shock Due to Ground Fault Occurrences. Meeting National Electrical Code Requirements For Ground Fault Protection, Gfci Receptacles Make It Easier to Recognize and Fix Trips Right Where They Happen – No More Confusion At The Breaker Box. Also Including Tamper and Weather Resistance, This Model Was Designed For Use On Decks, Patios, Pool Areas, and Other Outdoor Spaces. Maxim
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	15
connection	Back and side wire
indoor/outdoor	Outdoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Self-Test, Weather-Resistant, GFCI, Tamper-Resistant
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	RADIANT SELF TEST TR WR GFCI 15A 125V GY
extra long description	P&S 1597TRWRGRY RADIANT SELF TEST T
Long Description	GFCI receptacles from the radiant Registered Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Also including tamper and weather resistance, this model was designed for use on decks, patios, pool areas, and other outdoor spaces. Maxim
Product Type	Radiant Self Test TR WR Gfci 15A 125V Gy
Special Features	Spec Grade, Weather Resistant

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007036114
Manufacturers Part Number	1597-TRWRGRY
UPC	785007036114

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
nema rating	15A
Operating Temperature	-35°C to +66°C
standard	UL, CULUS, cULus, UL Listed, FSUL