



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1616612 Encl 16X16X6 N12 1DR CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	1616612
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 16" Height, 6" Length, 16" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	18.3 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	6.0000 IN X 16.0000 IN X 16.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	16.00 In Width X 6.00 In Depth X 16.00 In Height
------	--

Descriptions

Description	ENCL 16X16X6 N12 1DR CH CLAMP CVR
extra long description	B-LINE 16166-12 TYPE 12 SGL-DOOR EN
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 16" height, 6" length, 16" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 16X16X6
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051406887
Manufacturers Part Number	16166-12
UPC	782051406887

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	18.2919

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - AftermarketCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyUtility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings / Structures - Power Distribution and ControlsCommercial / Institutional Buildings / Structures - Critical PowerC
Mounting standard	EXTERNAL FEET, WALL UL 508A, NEMA, CSA C22.2.