



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1616812 Encl 16X16X8 N12 1DR CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	1616812
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 16" Height, 8" Length, 16" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	20.3 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

dimensions	8.0000 IN X 16.0000 IN X 16.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

### Dimensions and Weight

Size	16.00 In Width X 8.00 In Depth X 16.00 In Height
------	--

### Descriptions

Description	ENCL 16X16X8 N12 1DR CH CLAMP CVR
extra long description	B-LINE 16168-12 TYPE 12 SGL-DOOR EN
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 16" height, 8" length, 16" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 16X16X8
Special Features	Plated door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051406962
Manufacturers Part Number	16168-12
UPC	782051406962

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	20.314

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Commercial / Institutional Buildings / Structures - Critical Power Commercial / Institutional Buildings / Structures - Safety and Security Systems Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Other IT and Datacom - IT and Datacomm - Other Generation - Renewable Energy - Alternative Energy Datacente
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	UL 508A,NEMA,CSA C22.2.