



# Commercial grade receptacles


## Commercial grade straight blade receptacles

### Product description


2-pole, 3-wire grounding  
Dual voltage  
15A, 125/250V/AC  
NEMA 5-15R, 6-15R




829



826



815



1876

### Dual voltage commercial grade receptacle




Rating		NEMA	Description	Color	Catalog no.	
A	V/AC					
15	125/ 250	5-15R/ 6-15R	Dual voltage duplex receptacle, side wire	V	□ 829V	

## Commercial grade straight blade receptacles

### Product description

2-pole, 3-wire grounding  
15A, 250V/AC  
20A, 250V/AC  
NEMA 6-15R, 6-20R



### Commercial grade receptacles



Rating		NEMA	Description	Color suffix	Catalog no.	
A	V/AC					
15	250	6-15R	Duplex receptacle, side wire	B, V, W	□ 826_Δ	
			Single receptacle, side wire	B, V, W	□ 816_	
20	250	6-20R	Duplex receptacle, side wire	B, V, W	□ 815_Δ	
			Single receptacle, side wire	A, B, BK, LA, V, W	□ 1876_	

<sup>Δ</sup> Fed Spec certified

### Decorator commercial grade receptacle



Rating		NEMA	Description	Color	Catalog no.	
A	V/AC					
20	250	6-20R	Single receptacle, back & side wire	W	□ 6450W	

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), LA (Light Almond), V (Ivory), W (White)

<b>A</b>	<b>B</b>	<b>BK</b>	<b>LA</b>	<b>V</b>	<b>W</b>
(Almond)	(Brown)	(Black)	(Lt. Almond)	(Ivory)	(White)

**Specification information:** Commercial receptacles: A-33

**Compliances, specifications and availability are subject to change without notice.**

Build-to-spec customizable devices - Page A-6

Indicates NAFTA compliant - Page Q-32



RoHS compliant - Page Q-32

# Commercial grade receptacles


## Commercial grade straight blade receptacles

### Product description


2-pole, 3-wire grounding  
Dual voltage  
15A, 125/250V/AC  
NEMA 5-15R, 6-15R




829



826



815



1876


### Dual voltage commercial grade receptacle

Rating		NEMA	Description	Color	Catalog no.	
A	V/AC					
15	125/ 250	5-15R/ 6-15R	Dual voltage duplex receptacle, side wire	V	□ 829V	








## Commercial grade straight blade receptacles

### Product description

2-pole, 3-wire grounding  
15A, 250V/AC  
20A, 250V/AC  
NEMA 6-15R, 6-20R



### Commercial grade receptacles

Rating		NEMA	Description	Color suffix	Catalog no.	  
A	V/AC					
15	250	6-15R	Duplex receptacle, side wire	B, V, W	□ 826_Δ	
			Single receptacle, side wire	B, V, W	□ 816_	
20	250	6-20R	Duplex receptacle, side wire	B, V, W	□ 815_Δ	
			Single receptacle, side wire	A, B, BK, LA, V, W	□ 1876_	


<sup>Δ</sup> Fed Spec certified

### Decorator commercial grade receptacle

Rating		NEMA	Description	Color	Catalog no.	  
A	V/AC					
20	250	6-20R	Single receptacle, back & side wire	W	□ 6450W	

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), LA (Light Almond), V (Ivory), W (White)



**Specification information:** Commercial receptacles: A-33

**Compliances, specifications and availability are subject to change without notice.**

 Build-to-spec customizable devices - Page A-6

 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32