

# Eaton 1MCB800R

Catalog Number: 1MCB800R

Eaton main circuit breaker, 800 A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, MDL, Three-wire, Single-phase, 120/240V, (3) #3/0 AWG-400 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton main circuit breaker	1MCB800R
<b>UPC</b>	<b>Product Length/Depth</b>
786849053215	13.8 in
<b>Product Height</b>	<b>Product Width</b>
47.6 in	20.2 in
<b>Product Weight</b>	<b>Warranty</b>
120 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed	If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil]. Add CL to end of catalog number for compression lug pads (includes lug pads for lines and neutral).

## Product specifications

### Amperage Rating

800 A

### Bus material

Aluminum

### Feed type

Top/bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

NC : Dominion

VA : Dominion

### Enclosure

NEMA 3R

### Interrupt rating

65 kAIC

### Main circuit breaker

MDL

### Number of wires

3

### Wire size

(3) #3/0 AWG-400 kcmil

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - 1MCB800R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton 1MCB800R

Catalog Number: 1MCB800R

Eaton main circuit breaker, 800 A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, MDL, Three-wire, Single-phase, 120/240V, (3) #3/0 AWG-400 kcmil



## General specifications

### Product Name

Eaton main circuit breaker

### Catalog Number

1MCB800R

### UPC

786849053215

### Product Length/Depth

13.8 in

### Product Height

47.6 in

### Product Width

20.2 in

### Product Weight

120 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil]. Add CL to end of catalog number for compression lug pads (includes lug pads for lines and neutral).

## Product specifications

### Amperage Rating

800 A

### Bus material

Aluminum

### Feed type

Top/bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

NC : Dominion

VA : Dominion

### Enclosure

NEMA 3R

### Interrupt rating

65 kAIC

### Main circuit breaker

MDL

### Number of wires

3

### Wire size

(3) #3/0 AWG-400 kcmil

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - 1MCB800R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)