



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2006SB Copper Splice Cap Crimp Conn, 18-10 Awg, 1, 000/Bag

Ideal

| | |
|------------------|---|
| Catalog Number | 2006SB |
| Manufacturer | Ideal |
| Description | Buchanan, Crimp Connector, Splice Cap, Conductor Range: 18 - 10 Awg, 18/2 Awg Min, 12/4 Awg Max, Finish: Zinc-Plated, Tin-Plated Steel Sleeves, Material: Copper Sleeves, Voltage Rating: 600 V |
| Weight per unit | 0.0020 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|----------------|
| Material | Copper Sleeves |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|--------|---------------------------------------|
| Finish | Zinc-Plated, Tin-Plated Steel Sleeves |
|--------|---------------------------------------|

Descriptions

| | |
|------------------------|---|
| Description | COPPER SPLICE CAP CRIMP CONN, 18-10 AWG, 1,000/BAG |
| extra long description | IDEAL 2006SB SPLICE CAP 10,000 BX |
| Features | Designed for making fast, permanent, pressure-type connectionsSolid copper sleeves require less crimping pressure and resistn corrosion in harsh environmentsUL 486S Listed and CSA C22.2 #188 Certified: comply with Federal Specification W-S-61D |
| Long Description | Buchanan, Crimp Connector, Splice Cap, Conductor Range: 18 - 10 AWG, 18/2 AWG Min, 12/4 AWG Max, Finish: Zinc-Plated, Tin-Plated Steel Sleeves, Material: Copper Sleeves, Voltage Rating: 600 V |
| Product Type | Splice Cap 10, 000 BX |
| Special Features | Features: For #18 To #10 AWG Wire; Minimum 2 #18 AWG; Maximum 4 #12 AWG; Use Buchanan C24 Crimp Tool; Designed For Fast, Permanent, Pressure-Type Connections; UL Listed And CSA Certified; Zinc-Plated Or Copper Sleeves Resist Corrosion; Solid Copper Sleeves Require Less Crimping Pressure; Resist Corrosion In Harsh Environments; UL 486C Listed And CSA C22.2 #188 Certified; Comply With Federal Specification W-S-61D |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Buchanan |
| GTIN | 00781789452913 |
| Manufacturers Part Number | 2006SB |
| UPC | 781789452913 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | Splice Cap |

Packaging

| | |
|-----------------|-------|
| Carton | 10000 |
| Weight Per each | 0.002 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | For Buchanan C24 Crimp Tool And Designed For Fast, Permanent, Pressure-Type Connections |
| standard | CSA, UL Listed, RoHS |