



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2020612 Encl NM12 Encl *Cooper B-Line/Cable Tray*

Catalog Number	2020612
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 20" Height, 6" Length, 20" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	25.2 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	6.0000 IN X 20.0000 IN X 20.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	20.00 In Width X 6.00 In Depth X 20.00 In Height
------	--

Descriptions

Description	ENCL NM12 ENCL
extra long description	B-LINE 20206-12 TYPE 12 SGL-DOOR EN
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 20" height, 6" length, 20" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 20X20X6
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051800203
Manufacturers Part Number	20206-12
UPC	782051800203

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	25.175

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper Converged Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Safety and Security Systems Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Strctures - Aftermarket Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Critical Power Commercial / Institutional Buildings / Structures - Building Automation and Monit
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	UL 508A,NEMA,CSA C22.2.