



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 20308R 250V 30A 3P BXR R Fuse Block

*Mersen Fuses*

|                  |  |
|------------------|--|
| Catalog Number   | 20308R   |
| Manufacturer     | Mersen Fuses   |
| Description      | Fuse Block 250VAC 250VDC Class R 30A 3-Pole Box With Reinforced Clip |
| Weight per unit  | 0.2400 (lbs/each)  |
| Product Category | Fuseholders & Fuseblks   |

### Features

|                               |                            |
|-------------------------------|----------------------------|
| AC Voltage Rating             | 250                        |
| amperage rating               | 30                         |
| class                         | Class R                    |
| connection                    | Box with Reinforced Clip   |
| DC Voltage Rating             | 250                        |
| Material                      | Glass Filled Polycarbonate |
| Maximum Operating Temperature | 80                         |
| Phase                         | 3                          |
| Poles                         | 3-Pole                     |
| Voltage Rating                | 250                        |

### Dimensions and Weight

|      |              |
|------|--------------|
| Size | 3 x 3 x 1.38 |
|------|--------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 250V 30A 3P BXR R FUSE BLOCK  |
| extra long description | Mersen 20308R Fuse Block 250VAC 250   |
| Features               | Mersen Class H, K and R fuse blocks accommodate all Class H, K and R 250 and 600V power fuses. A choice of screw, pressure plate, box and special order stud connectors fit a wide range of stranded or solid copper or aluminum wire. Insulators are either molded glass-filled polycarbonate (GFPC) or phenolic with verified dielectric strength in excess of 2500V. 30, 60 and 100A fuse blocks feature a unique adder block which can be snapped onto 1-, 2- or 3-pole blocks to form multipole segmented blocks of as man |
| Long Description       | Fuse Block 250VAC 250VDC Class R 30A 3-Pole Box with Reinforced Clip  |
| Product Type           | Fuse Block 250VAC 250VDC Class R 30A 3-Pole Box With Reinfor  |
| Short Description      | R FUSE BLOCK 250V 30A 3P BXR  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Mersen         |
| GTIN                      | 00782001750428 |
| Manufacturers Part Number | 20308R         |
| UPC                       | 782001750428   |

## Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | FUSE BLOCKS,FUSE HOLDERS |
| Type                 | UL/CSA Fuse Bases        |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 5    |
| Weight Per each | 0.24 |

## Uses, Certifications, and Standards

|          |   |
|----------|---|
| Mounting | Direct Screw Mount  |
| standard | All fuse blocks meet the requirements of UL 4248 UL listed, guide IZLT, File E52283 UL recognized component guide IZLT2, file E52283 CSA certified class 6225, File 32169 |