



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRGRY Radiant Self Test TR Gfci 20A 125V Gy

Pass & Seymour/LeGrand

| | |
|------------------|---|
| Catalog Number | 2097TRGRY |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Gfci Receptacles From The Radiant Registered Collection Self-Test Automatically Every Three Seconds to Ensure Reliable Protection From Shock Due to Ground Fault Occurrences. Meeting National Electrical Code Requirements For Ground Fault Protection, Gfci Receptacles Make It Easier to Recognize and Fix Trips Right Where They Happen – No More Confusion At The Breaker Box. 20A Outlets Are Ideal For Use With Larger Appliances and In Commercial Settings, As Well As to Meet Regional Requirements (Chicago, Canada) |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|-----------------------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| indoor/outdoor | Indoor |
| interrupt rating | 4 to 6 mA |
| Material | Thermoplastic |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Outlet Type | Self-Test, Tamper-Resistant, GFCI |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage Rating | 125 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 4.2 |
| Length | 1.03 |
| Width | 1.73 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SELF TEST TR GFCI 20A 125V GY |
| extra long description | P&S 2097TRGRY RADIANT SELF TEST TR |
| Long Description | GFCI receptacles from the radiant Registered Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada) |
| Product Type | Radiant Self Test TR Gfci 20A 125V Gry |
| Special Features | Spec Grade |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007036282 |
| Manufacturers Part Number | 2097-TRGRY |
| UPC | 785007036282 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------------|
| Application | Commercial/Residential |
| environmental conditions | 95% Humidity, UL 94 V2 |
| Frequency Rating | 60 Hz |
| nema rating | 20A |
| Operating Temperature | -35°C to +66°C |
| standard | UL, CULUS, cULus, UL Listed, FSUL |