



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20U Breakaway Streetlight Kit, In-Line Non-Fused, Neut

Ideal

Catalog Number	20U
Manufacturer	Ideal
Description	Buchanan, In-Line Neutral Kit, Breakaway In-Line Kits, Non-Fused, Voltage Rating: 600 V, Amperage Rating: 30 Amp, Line Side Cable Size: 12 - 6 Awg, Line Side Crimp Type: Copper, Line Side Insulation Diameter: .120 - .430 In, Load Side Cable Size: 12 - 6 Awg, Load Side Crimp Type: Copper, Load Side Insulation Diameter: .120 - .430 In
Weight per unit	0.2400 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

amperage rating	30
Voltage Rating	600

Descriptions

Description	BREAKAWAY STREETLIGHT KIT, IN-LINE NON-FUSED, NEUT
extra long description	IDEAL 20U LV KIT
Features	Buchanan Breakaway Connector Kits are designed for use in highway lighting, area lighting, flood lighting, and power distribution circuits in the wire range of #14 to #2 AWG. The kits install easily in 5 minutes or less using only a knife, wire stripper, and crimp tool – eliminating the need for special equipment, potting, tape, extra crimp inserts, resins, and cure time. The built in “breakaway” design prevents broken wires and the de-energization of a complete circuit when one component, such as a light s
Long Description	Buchanan, In-Line Neutral Kit, Breakaway In-Line Kits, Non-Fused, Voltage Rating: 600 V, Amperage Rating: 30 AMP, Line Side Cable Size: 12 - 6 AWG, Line Side Crimp Type: Copper, Line Side Insulation Diameter: .120 - .430 IN, Load Side Cable Size: 12 - 6 AWG, Load Side Crimp Type: Copper, Load Side Insulation Diameter: .120 - .430 IN
Product Type	LV Kit
Special Features	Line Side Cable Size: 12 - 6 AWG; Line Side Crimp Type: Copper; Line Side Insulation Diameter: .120 - .430 IN; Load Side Cable Size: 12 - 6 AWG; Load Side Crimp Type: Copper; Load Side Insulation Diameter: .120 - .430 IN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Ideal
GTIN	00781789002637
UPC	781789002637

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Breakaway In-Line Kits, Non-Fused

Packaging

Carton	1
Weight Per each	0.24

Uses, Certifications, and Standards

Application	In-Line Neutral, Non-Fused Breakaway
standard	RoHS