



## Standard size duplex receptacle wallplates

### Product description


1-Gang, 2-Gang, 3-Gang




1-Gang



2-Gang





3-Gang



1-Gang

### Duplex receptacle



Gang	Material	Color suffix	Catalog no.	 
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5132__	• •
	Thermoset	A, B, LA, V, W	□ 2132__	• •
	302/304 Stainless steel	—	□ 93101	• •
	Brass	—	□ 94101	• •
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5150__	• •
	Thermoset	A, B, LA, V, W	□ 2150__	• •
	302/304 Stainless steel	—	□ 93102	• •
	Brass	—	□ 94102	• •
3-Gang	302/304 Stainless steel	—	□ 93103	• •

## Standard size single receptacle wallplates

### Product description











1-Gang

### Single receptacle

Gang	Material	Color suffix	Catalog no.	 
1-Gang with 1.406" (35.712mm) hole	Nylon	A, B, BK, GY, RD, V, W	□ 5131__	• •
	Thermoset	A, B, LA, V, W	□ 2131__	• •
	302/304 Stainless steel	—	□ 93091	• •
	Brass	—	□ 94091	• •

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)

 A	 B	 BK	 GY	 LA	 RD	 V	 W
(Almond)	(Brown)	(Black)	(Gray)	(Lt. Almond)	(Red)	(Ivory)	(White)
							
(Stainless Steel)	(Brass)						

**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**


 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32


## Standard size duplex receptacle wallplates

### Product description


1-Gang, 2-Gang, 3-Gang




1-Gang



2-Gang



3-Gang



1-Gang

### Duplex receptacle

Gang	Material	Color suffix	Catalog no.	
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5132__	• •
	Thermoset	A, B, LA, V, W	□ 2132__	• •
	302/304 Stainless steel	—	□ 93101	• •
	Brass	—	□ 94101	• •
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5150__	• •
	Thermoset	A, B, LA, V, W	□ 2150__	• •
	302/304 Stainless steel	—	□ 93102	• •
	Brass	—	□ 94102	• •
3-Gang	302/304 Stainless steel	—	□ 93103	• •

## Standard size single receptacle wallplates

### Product description


1-Gang

### Single receptacle

Gang	Material	Color suffix	Catalog no.	
1-Gang with 1.406" (35.712mm) hole	Nylon	A, B, BK, GY, RD, V, W	□ 5131__	• •
	Thermoset	A, B, LA, V, W	□ 2131__	• •
	302/304 Stainless steel	—	□ 93091	• •
	Brass	—	□ 94091	• •

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32