



Standard size wallplates toggle switch

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang



4-Gang





5-Gang



6-Gang


Toggle switch wallplates

Gang	Material	Color suffix	Catalog no.		
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5134__	•	•
	Thermoset	A, B, LA, V, W	□ 2134__	•	•
	302/304 stainless steel	—	□ 93071	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93071__	•	•
	Brass	—	□ 94071	•	•
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5139__	•	•
	Thermoset	A, B, LA, V, W	□ 2139__	•	•
	302/304 stainless steel	—	□ 93072	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93072__	•	•
	Brass	—	□ 94072	•	•
3-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5141__	•	•
	Thermoset	A, B, LA, V, W	□ 2141__	•	•
	302/304 stainless steel	—	□ 93073	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93073__	•	•
	Brass	—	□ 94073	•	•
4-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5154__	•	•
	Thermoset	A, B, LA, V, W	□ 2154__	•	•
	302/304 stainless steel	—	□ 93074	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93074__	•	•
5-Gang	Thermoset	A, B, LA, V, W	□ 2155__	•	•
	302/304 stainless steel	—	□ 93075	•	•
6-Gang	Thermoset	A, B, V, W	□ 2156__	•	•
	302/304 stainless steel	—	□ 93076	•	•

See additional CuVerro® wallplate information on K-22

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), CU (White Bronze) CuVerro® ONLY, CUR (Rose) CuVerro® ONLY



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified; CuVerro® series wallplates are only UL Listed. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.


 Indicates NAFTA compliant - Page Q-30

 RoHS compliant – Page Q-30


Standard size wallplates toggle switch

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang



4-Gang





5-Gang



6-Gang


Toggle switch wallplates

Gang	Material	Color suffix	Catalog no.	 
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5134__	• •
	Thermoset	A, B, LA, V, W	□ 2134__	• •
	302/304 stainless steel	—	□ 93071	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93071__	• •
	Brass	—	□ 94071	• •
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5139__	• •
	Thermoset	A, B, LA, V, W	□ 2139__	• •
	302/304 stainless steel	—	□ 93072	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93072__	• •
	Brass	—	□ 94072	• •
3-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5141__	• •
	Thermoset	A, B, LA, V, W	□ 2141__	• •
	302/304 stainless steel	—	□ 93073	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93073__	• •
	Brass	—	□ 94073	• •
4-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5154__	• •
	Thermoset	A, B, LA, V, W	□ 2154__	• •
	302/304 stainless steel	—	□ 93074	• •
	CuVerro® antimicrobial copper	CU, CUR	□ 93074__	• •
	Brass	—	□ 94074	• •
5-Gang	Thermoset	A, B, LA, V, W	□ 2155__	• •
	302/304 stainless steel	—	□ 93075	• •
6-Gang	Thermoset	A, B, V, W	□ 2156__	• •
	302/304 stainless steel	—	□ 93076	• •

See additional CuVerro® wallplate information on K-22

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), CU (White Bronze) CuVerro® ONLY, CUR (Rose) CuVerro® ONLY



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified; CuVerro® series wallplates are only UL Listed. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page Q-30

 RoHS compliant – Page Q-30