



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



22SRLD229CUNVL8 22srlld229cunvl840cd1u *Cooper Lighting Solutions*

| | |
|------------------|---|
| Catalog Number | 22SRLD229CUNVL8 |
| Manufacturer | Cooper Lighting Solutions |
| Description | Led, 2'X2' Skyridge, Wavestream, 2900 Lumens, 85 Cri, 4000K, Unv 0-10V Dimming Driver, Curved |
| Weight per unit | 14.0 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|---------------|
| amperage rating | 0.084 at 277V |
| Ballast Type | N/A |
| Lamp Type | LED |
| Material | Aluminum |
| Number of Lamps | 1 |
| Socket Type | N/A |
| Voltage Rating | 120/277V |

Material, Color, and Finish

| | |
|-------|---------|
| Style | (blank) |
|-------|---------|

Descriptions

| | |
|------------------------|---|
| extra long description | CLS 22SR-LD2-29-C-UNV-L840-CD1-U 2X |
| Long Description | LED, 2'x2' SkyRidge, WaveStream, 2900 Lumens, 85 CRI, 4000K, UNV 0-10V Dimming Driver, Curved |
| Product Type | 2X2 Led Sky RDG, 2900, 40K, Unv 0-10V DD |
| Special Features | Available in 1' x 2', 1' x 4', 2' x 2' and 2' x 4' recessed versions |

Manufacturer Information

| | |
|---------------------------|------------------------------|
| Brand | METALUX |
| GTIN | 00080083752577 |
| Manufacturers Part Number | 22SR-LD2-29-C-UNV-L840-CD1-U |
| UPC | 080083752577 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | Recessed Static |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 14 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | lighting |
| Mounting | Recessed |
| standard | UL Recognized;cULus Listed;LM79/LM80 Compliant;DLC Qualified;IC Rated;RoHS Compliant;Damp Locations Listed;NOM Certified;25 Degree C Ambient Temperature Rating |